







EG TEC

is a creator and leader of technology for healthy human life





Greetings

EG Tec is a product development, production and sales company. We are able to develop and manufacture ODM and OEM products per customer's request. EG Tec's dedicated R&D center is officially recognized by the state. All of our products are managed and manufactured by the ISO 9001:2015 Quality Management System and the quality of the product is managed by CE Certification system





- 2010.07 Acquired a patent for cylinder type pressure reducing valve. (2012.08 patent acquisition).
- 2011. 09 Developed and acquired a patent for instant water heating system.
- 2012. 04 Exported sparkling mist to Japan.
- 2013. 05 Developed and acquired a patent for water purifier valve system.
- 2013. 10 Established EG Tec R&D Center.
- 2013. 12 Developed and acquired a patent for UV sterilization lamp.
- 2014. 08 Quality management system certified. (ISO)
- 2015. 08 Developed hydrogen water purifier.
- 2016. 05 Developed electrolytic cell module for large capacity hydrogen water purifier Patent application under review.
- 2017. 06 Developed world's first hydro water purifier for large capacity PEM mode shower.
- 2017. 11 Developed portable high concentration hydro water purifier.
- 2018. 12 Developed automotive air cleaner using silicon carbide filter.
- 2019. 05 Developed and acquired a patent for kettle type hydrogen water generator.
- 2019. 11 Necklace air purifier under development.

Certificated




























The EGP-1000T product developed by EG Tec is made from a traditional glass bottle-based hydrogen generator for newborns, babies-only Tritan Bottle material. Tritan bottle is an eco-friendly new material used as a newborn baby bottle. The new material of Tritan can be used up to -20°C ~110°C and is an eco-friendly product that does not produce environmental hormones.



Product Specifications


- High dissolved hydrogen concentration over 1000ppb
- Dissolved hydrogen concentration is maintained for a longtime
- Ozone isseparated by diaphragm (PEM) separating hydrogen from oxygen (No disgusting odors in water)
- Cleanliness by using specially treated membrane
- 🐼 Hydrogen water generation at any place even if based on charging mode
- 放 High concentration hydrogen water generation by RO purified water
- 2stages of time option(5 and 8 minute)

Electrolysis



Key Specifications

Model	EGP-1000T
Capacity	350 cc
DH concentration	About 1000 ppb
ORP	-350 ∼ -550 mV
Using temp. range	5 ~ 40 °C
Weight	About 360 g (body weight)
Dimension	W 70 × D 70× H 220 mm
Operating time	5 / 8 min
No. of uses	5 min: 35 ~ 50 times /, 8 min: 25 ~ 35 times
Charging time	App. 90 ~ 150 min
Rated voltage	DC 3.7 V
Shipping quantity in a container (20ft: 4,800 / 40ft: 9,600 / H40ft: 11,200)	



www.egtplus.com



EG TEC is a creator and leader of water technology for human health life.



www.egtplus.com

e-mail: egtplus@hanmail.net, egtplussales@naver.com TEL: +82 (0)70 4814 - 4901 ADD: EG Tec 1 Fl. 317 - 59 Seja-Ro, Jeongnam-Myun, Hwaseong-Si, Kyunggi-Do, Korea Postal Code 18516